

## ETL SELF-REGULATING HEATING CABLE

nVent RAYCHEM ETL self-regulating trace heating cables provide energy efficient pipe freeze protection. R-ETL-A/B are suitable for on- or in-pipe applications, R-ETL(-A/B)-CR for on-pipe only. Each are available in two power outputs (10 and 16 W/m at 5 °C), supported by a full range of heat shrinkable connections and accessories.



### FEATURES & BENEFITS

---

Simple to design, with fluoropolymer jacket option for use in pipes

Easy to install: small geometry, cut to length, meter marks

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year product warranty available, maintenance free

### SPECIFICATIONS

---

**Supply Voltage** 220 – 240 V

**Color** Black

**Nominal Width** 8.5 mm

**Nominal Thickness** 5.8 mm

**Ground Path Type** Braid

**Min Installation Temperature** -20 °C

**Conductor Material** Nickel-Plated Copper

**Max Continuous Exposure Temperature, Power Off** 65 °C

**Min Bending Radius** 10 mm

Table 1/1

Catalog Number	Item Name	Nominal Power Output, In-Pipe @ 230V	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Max Circuit Length, In-Pipe
924269-000	R-ETL-A	16 W/m	10 W/m	100 m	60 m

Maximum circuit lengths are based on 230 VAC supply and C-Type characteristic circuit protection devices, switch-on at 5 °C.

#### North America

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

#### Europe, Middle East, Africa

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

#### Asia Pacific

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

#### Latin America

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
 nVent reserves the right to change specifications without notice.